



# **DYNAMIC**

## **GD4200-USB**

### **USB PRESSURE TRANSDUCER**



- Sample rate software selection up to 1,000 Hz
- Silicon-on-Sapphire pressure sensor technology
- Choice of pressure ranges from vacuum to 5,000 bar
- Accuracy (NLHR)  $\pm 0.15\%$  of span BFSL
- Auto detect and configuration
- USB 2.0 compatible
- ESI-USB© downloadable software with auto update
- Measure & record up to 16 pressure inputs together
- Create customised test certificate
- Automatic temperature compensation
- Support for easy integration with applications created by C#, VB, Labview and Excel VBA (api dll library)
- 2m lead & carry case included



## Description

The GD4200-USB® Digital Pressure Transducer has been designed to measure, analyse and record pressure directly on your PC without the need for costly I/O interface boards. It allows the user to measure up to 16 pressure inputs simultaneously and easily create customised test certificates.

The transducer is USB 2.0 compatible and connects via a detachable USB lead. The data is captured by the ESI-USB® configurable Windows Interface software, and presented on-screen in real-time without loss of accuracy or bandwidth. It is compatible with Windows® 8, 8.1 and 10 and configures automatically with your desktop, laptop or tablet via USB protocol. It has instant connection and will automatically detect when a sensor is connected. The sample rate enables dynamic pressures to be measured with up to 21 bit resolution at user selectable speeds up to 1,000 Hz. Data can be displayed in graphical or tabular form, with a choice of pressure units and fully adjustable scales. Data can be saved to a file or exported to Excel, PDF and .csv.

The ESI-USB software has many features including certificate generation, customisable certificate templates, leak testing, measure, record and view up to 16 sensors at the same time, virtual differential pressure measurement, set automatic test start and stop times, and alarm levels for each individual sensor. We are continually enhancing the ESI-USB software, and the auto-update feature means that you will never miss a new version.


The unique Silicon-on-Sapphire sensor technology provides outstanding performance and gives excellent stability over a wide temperature range. Excellent measurement accuracy provides high resolution with a precision greater than 1 in 10,000. Nine pressure ranges have been carefully selected to enable the user to cover any pressure that the application requires, from vacuum up to 5,000 bar, via the use of the ESI-USB® digitally self scaling software.

Each unit requires free download of the ESI-USB® software and is supplied with 2m USB lead (rated to IP68), and a convenient carry case.

## Dimensions (in mm)



## ESI-USB Software



Graph Screen



Monitor Screen

## Technical Data

Type	GD4200-USB
Sensor Technology:	Silicon-on-Sapphire (SoS)
Output Signal:	USB 2.0 compatible
Supply Voltage:	5 VDC via USB bus
Pressure Reference:	Gauge (default); Absolute reference input by user
Standard Pressure Ranges:	-1 to 2.5 bar; 0 – 16 bar; 0 – 100 bar; 0 – 400 bar; 0 – 1,000 bar; 0 – 1,500 bar; 0 – 2,000 bar; 0 – 4,000 bar; 0 – 5,000 bar
Standard Pressure Ranges (other):	User selectable for psi and other measurement units
Overpressure Safety:	2x up to 400 bar; 1.5x for 1,000 bar; 1.1x for 1,500 bar; 1.5x for 2,000 bar; 1.25x for 4,000 bar; 1.2x for 5,000 bar;
Accuracy NLHR:	$\leq \pm 0.15\%$ of span BFSL
Sample Rate:	User selectable to 1,000 samples per second (1,000 Hz) Resolution: 21 bits for $\leq 5$ Hz; 16 bits for $> 5 - 1,000$ Hz
Operating Ambient Temperature:	-20 °C to +85 °C (-4 °F to +185 °F)
Operating Media Temperature:	-50 °C to +125 °C (-58 °F to +257 °F)
Storage Temperature:	+5 °C to +40 °C (+41 °F to +104°F) Recommended Best Practice
Temperature Effects:	$\pm 1.5\%$ FS total error band for -10 °C to +80 °C. Typical thermal zero and span coefficients $\pm 0.015\%$ FS/ °C
Electromagnetic Compatibility:	EN61326-1, EN61326-2-3 (Laboratory equipment)
Wetted Parts:	Titanium alloy
Pressure Media:	All fluids compatible with titanium alloy
Pressure Connection:	1/4" BSP male (G1/4); 1/4" NPT male or F250-C (Autoclave)
Electrical Connection:	Mating to USB mini B socket for cable connection to PC. Supplied with 2m USB lead rated to IP68 as standard.
Software compatibility:	Windows 8, Windows 8.1 and Windows 10
Net. Weight (Kg):	0.4 Kg

## Order Matrix

Output	Type	Electrical Connection	Pressure Range	Process Connection
Dynamic (1,000 Hz)	GD4200-USB			
<b>Electrical Connection</b>				
Mating to USB mini B socket		-		
<b>Pressure Range in bar</b>				
-1 to 2.5 bar			02.5	
0-16 bar			0016	
0-100 bar			0100	
0-400 bar			0400	
0-1,000 bar			1000	
0-1,500 bar			1500	
0-2,000 bar			2000	
0-4,000 bar			4000	
0-5,000 bar			5000	
<b>Process Connection</b>				
1/4" BSP male (G1/4)				AB
1/4" NPT male				AM
Autoclave F-250-C female (for pressures above 1,500bar)				DE

## Order Number Example

GD4200-USB1500AB

For options not listed please contact the sales team



株式会社 クローネ

■ カタログに掲載してある製品の色は印刷インキの関係上、実際とは異なる場合があります。  
 ■ 製品のデザイン、仕様等などは、予告なく変更する場合があります。

本 社：〒124-0023 東京都葛飾区東新小岩3丁目9番6号 TEL: (03) 3695-5431 / FAX: (03) 3695-5698  
 大阪支店：〒530-0054 大阪府北区南森町2-2-9 (南森町八千代ビル7F) TEL: (06) 6361-4831 / FAX: (06) 6361-9360  
 e-mail: sales-tokyo@krone.co.jp URL: <https://www.krone.co.jp>

**DISCLAIMER :** ESI Technology Ltd operates a policy of continuous product development. We reserve the right to change specification without prior notice. All products manufactured by ESI Technology Ltd are calibrated using precision calibration equipment, traceable to national measurement standards.



t. +44(0)1978 262 255  
 e. sales@esi-tec.com

[www.esi-tec.com](http://www.esi-tec.com)
